

Quick & Easy

Simplified Tensile Tester

PT-3000DG-P

Grasping the weld strength and meeting the requirements are essential when high welding quality is demanded!

Are you sure your weld is strong enough? How can you explain how good your weld is?-----This Simplified Tensile Tester can be your solution.



Place a spotwelded sample on the machine.



Pull it until the welded surface comes apart.




The shear strength is shown as a numeral. Press the print button to print the result.




Print out the result.

Space saving design!



Printer attached.

Spacer is included for testing nuts.



PT-3000DG-P

Model	PT-3000-DG-P
Max. Measuring capacity	30kN(Measurable range: 2kN to 30kN)
Accuracy	±10%
Load indication	Digital
Clamping method	Top/Bottomclamps
Pressing method:	Manual Lever (With hydraulic jack)
Test Sample dimensions:	JIS 3136 for single point (30mmx100mm)
Weight:	82kg
Dimensions:	H800xW460xD400mm, desktop

Koyo gikken inc.
4020-4 Tana Chuo-ku Sagamihara Kanagawa 252-0244 JAPAN
Tel: 042-760-4306 Fax: 042-760-4309

koyo giken
www.koyogikken.co.jp

2016.04.01